

VP M32-MS65**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPMS (blanking plug in brass), Blanking plug, in closed state, M 32, 8 mm, Brass, nickel-plated
Order No.	177760000
Type	VP M32-MS65
GTIN (EAN)	4032248158034
Qty.	50 Stück

Erstellungs-Datum May 30, 2023 3:11:47 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

VP M32-MS65

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	12 mm	Height (inches)	0.472 inch
Length	12 mm	Length (inches)	0.472 inch
Diameter	35 mm	Wall thickness, max.	7 mm
Net weight	24.3 g		

Temperatures

Operating temperature	-40 °C...100 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	100 °C		

General information

Cable glands	metric	Diameter of sealing ring	32 mm
External thread	M 32	Halogen	No
Head diameter	35 mm	Length of thread	8 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Protection degree	IP68 - 5 bar (30 min.)
Sealing	NBR	Silicone	No

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-33	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25	ECLASS 12.0	27-14-08-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

VP M32-MS65

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

