

SAI-SK STECKER M12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Protective caps protect unassigned plug-in stations against external influences.

General ordering data

Version	Plug-in connector, IP20
Order No.	1781520000
Type	SAI-SK STECKER M12
GTIN (EAN)	4032248171835
Qty.	50 Stück

SAI-SK STECKER M12

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 0.82 g

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	80 °C

General technical data

Protection degree IP20

Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-02-08	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-08	ECLASS 12.0	27-44-02-08

Approvals

Approvals



ROHS Conform

Downloads

Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN