

## HDC 07A TWLU 1M20G

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

### General ordering data

Version	HDC enclosures, Size: 1, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 20
Order No.	<a href="#">1788510000</a>
Type	HDC 07A TWLU 1M20G
GTIN (EAN)	4032248206049
Qty.	1 pc(s).

## HDC 07A TWLU 1M20G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	37.3 mm	Depth (inches)	1.469 inch
Height	49.2 mm	Height (inches)	1.937 inch
Width	36.5 mm	Width (inches)	1.437 inch
Net weight	14 g		

## Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

## Dimensions

Cable entry	w. thread	Height of housing B	49.2 mm
Total length housing	37.3 mm	Width housing C	26.8 mm

## General data

EMC housings	No	Housing main material	Plastic
Protection degree	IP65 (in plugged condition)	Tightening torque	0.5 Nm
UL 94 flammability rating	V-0		

## Version

BG	1	Cable entry	w. thread
Clamp version	Side-locking clamp	Colour (RAL)	RAL 1001
Design	Standard	Design of housing	Cable entry from side, Plug housing
Design of locking system	Side-locking clamp on lower side	Internal thread	M 20
Number of cable entry on top	0	Number of cable entry sideways	1
Size	1	Size of cable entries	M 20
Suitable for ModuPlug®	No	Tightening torque	0.5 Nm
Top part/bottom part/lid	upper part	Type	Plug

## Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02

Substance	Acetone
Chemical resistance	Conditionally resistant
Substance	Drilling oil
Chemical resistance	Resistant
Substance	Diesel
Chemical resistance	Resistant
Substance	Ethyl alcohol
Chemical resistance	Resistant
Substance	Transmission oil
Chemical resistance	Resistant

Creation date February 23, 2023 11:01:28 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

2

## HDC 07A TWLU 1M20G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Coolant
Chemical resistance	Resistant
Substance	Petroleum benzine
Chemical resistance	Resistant
Substance	Sweat
Chemical resistance	Resistant
Substance	Premium gasoline
Chemical resistance	Conditionally resistant
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Unstable
Substance	Ozone
Chemical resistance	Unstable

## Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	2f94735a-9fba-4903-842f-4fb9aa902310
Chemical resistance	de.myview.objectmodel.impl.BlockImpl@7abae81 de.myview.objectmodel.impl.BlockImpl@5603f1ab de.myview.objectmodel.impl.BlockImpl@cfdf1ac6 de.myview.objectmodel.impl.BlockImpl@d68ba43 de.myview.objectmodel.impl.BlockImpl@576dd2c9 de.myview.objectmodel.impl.BlockImpl@1e2aff26 de.myview.objectmodel.impl.BlockImpl@7a65ed0f de.myview.objectmodel.impl.BlockImpl@3217eaa2 de.myview.objectmodel.impl.BlockImpl@bd58db3 de.myview.objectmodel.impl.BlockImpl@42cf9020 de.myview.objectmodel.impl.BlockImpl@171710e3 de.myview.objectmodel.impl.BlockImpl@1ad8aa59 de.myview.objectmodel.impl.BlockImpl@3dc714a4

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Product Change Notification	<a href="#">20220214 Technical change to HDC housings</a> <a href="#">20220214 Technische Änderung bei HDC-Gehäusen</a>
Technical Documentation	<a href="#">1788510000_HDC_07A_TWLU_1M20G_STP_Blatt__1.pdf</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

Creation date February 23, 2023 11:01:28 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

3

**HDC 07A TWLU 1M20G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

