

**WQL 3 WF5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

|            |   |
|------------|---|
| Version    | Bolt-type screw terminals, Cross-connector,<br>Number of poles: 3 |
| Order No.  | <a href="#">1812740000</a>  |
| Type       | WQL 3 WF5   |
| GTIN (EAN) | 403224840455 1  |
| Qty.       | 5 pc(s).  |

Creation date March 3, 2023 4:47:20 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## WQL 3 WF5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 4 mm    | Depth (inches)  | 0.157 inch |
| Height     | 38 mm   | Height (inches) | 1.496 inch |
| Width      | 12 mm   | Width (inches)  | 0.472 inch |
| Net weight | 13.08 g |                 |            |

## Temperatures

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

## Material data

|          |               |        |      |
|----------|---------------|--------|------|
| Material | Copper - zinc | Colour | grey |
|----------|---------------|--------|------|

## Additional technical data

|                     |                 |                |                 |
|---------------------|-----------------|----------------|-----------------|
| Installation advice | Direct mounting | Type of fixing | when screwed in |
|---------------------|-----------------|----------------|-----------------|

## Cross-connector

|                       |      |                           |       |
|-----------------------|------|---------------------------|-------|
| Rated current, 2-pole | 76 A | Rated current, multi-pole | 101 A |
|-----------------------|------|---------------------------|-------|

## Dimensions

|                 |       |
|-----------------|-------|
| Pitch in mm (P) | 13 mm |
|-----------------|-------|

## General

|                     |                 |                 |   |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 3 |
|---------------------|-----------------|-----------------|---|

## Rating data

|               |      |
|---------------|------|
| Rated current | 76 A |
|---------------|------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ECLASS 9.0  | 27-14-11-40 |
| ECLASS 9.1  | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 | ECLASS 12.0 | 27-14-11-40 |

## Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**WQL 3 WF5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">EAC certificate</a>                 |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                 |
| Engineering Data                            | <a href="#">WSCAD</a>                           |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>        |
| Brochures                                   |   |

---