


KOSF ZT4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Through the use of coding pins, individual coding options ensure trouble-free plug-in connection.

General ordering data

Version	Z-series, Coding element, Direct mounting
Order No.	1856860000
Type	KOSF ZT4
GTIN (EAN)	4032248400744
Qty.	50 pc(s).

Creation date February 23, 2023 4:17:50 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

KOSF ZT4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	2.23 mm	Depth (inches)	0.088 inch
Height	14.9 mm	Height (inches)	0.587 inch
Width	5.4 mm	Width (inches)	0.213 inch
Net weight	0.18 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50
Continuous operating temp., max.	100		

Material data

Material	PA 66 GF 30	Colour	beige
UL 94 flammability rating	HB		

System specifications

Version	Coding element
---------	----------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	