

**CBFP 43.5/10 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Fastening of cables or bundles with ties into electrical switchgears and cabinets.

**General ordering data**

Version	Cable ties, 10 x 10 mm, Plastic, 80 N
Order No.	<a href="#">1859410000</a>
Type	CBFP 43.5/10 BK
GTIN (EAN)	4032248412297
Qty.	100 Stück

## CBFP 43.5/10 BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	10 mm	Height (inches)	0.394 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	1.91 g		

### Temperatures

Operating temperature range	-40...100 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	100 °C		

### Installation materials

Diameter of fastening hole	8 mm	For re-opening	No
Material	Plastic	Max. cable tie width	9 mm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Tensile strength	80 N	Tensile strength (Pound-force)	18 lbf
UL 94 flammability rating	V-2	UV-resistant	No
Version	for wall mounting		

### Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## CBFP 43.5/10 BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen

### Dimensional drawing

