

**WAP WSI4/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

Version	W-Series, End plate
Order No.	<a href="#">1880450000</a>
Type	WAP WSI4/2
GTIN (EAN)	4032248541911
Qty.	50 pc(s).

## WAP WSI4/2

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	49.49 mm	Depth (inches)	1.948 inch
Height	71.12 mm	Height (inches)	2.8 inch
Width	2.5 mm	Width (inches)	0.098 inch
Net weight	6.52 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

## Material data

Material	Wemid	Colour	black
UL 94 flammability rating	V-0		

## System specifications

Version	End plate
---------	-----------

## Additional technical data

Installation advice	Feed-through (bushing)	Snap-on	No
---------------------	------------------------	---------	----

## Dimensions

TS 32 offset	36 mm	TS 35 offset	36 mm
--------------	-------	--------------	-------

## General

Installation advice	Feed-through (bushing)
---------------------	------------------------

## Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ECLASS 9.1	27-14-11-33
ECLASS 10.0	27-14-11-33	ECLASS 11.0	27-14-11-33
ECLASS 12.0	27-14-11-33		

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	