

WSMC 11-15

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

General ordering data

| | |
|------------|--|
| Version | Stainless steel markers, Conductor and cable markers, 93 x 10 mm, silver |
| Order No. | 1891670000 |
| Type | WSMC 11-15 |
| GTIN (EAN) | 4032248504305 |
| Qty. | 1 Stück |

WSMC 11-15

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.5 mm | Depth (inches) | 0.02 inch |
| Height | 93 mm | Height (inches) | 3.661 inch |
| Width | 10 mm | Width (inches) | 0.394 inch |
| Net weight | 3 g | | |

Temperatures

| | |
|-----------------------------|--------|
| Operating temperature range | 500 °C |
|-----------------------------|--------|

General data

| | | | |
|-----------------------------|---------------------------|-----------------------------------|--|
| Colour | silver | Material | Stainless steel 1.4404 |
| Number of characters | 15 | Number of markers per combination | 1 Component part = Conductor and cable markers |
| Operating temperature range | 500 °C | Operating temperature range, max. | 500 °C |
| Orientation of print | horizontal | Printed characters | Mixed characters |
| Type of printing | To customer specification | Width | 10 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |