

**MOFU 15/35 ZPS2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Mounting feet are used to mount components that cannot be snapped directly on a DIN rail.

**General ordering data**

Version	Z-series, Mounting foot, yellow, 5.1 mm
Order No.	<a href="#">1899170000</a>
Type	MOFU 15/35 ZPS2.5
GTIN (EAN)	4032248518708
Qty.	25 pc(s).

## MOFU 15/35 ZPS2.5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	21.47 mm	Depth (inches)	0.845 inch
Height	52.4 mm	Height (inches)	2.063 inch
Width	5.1 mm	Width (inches)	0.201 inch
Net weight	2.303 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50
Continuous operating temp., max.	120		

## Material data

Material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

## Dimensions

TS 15 offset	21 mm	TS 35 offset	2 mm
--------------	-------	--------------	------

## General

Installation advice	Direct mounting
---------------------	-----------------

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	