

WSMC 21-25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

General ordering data

Version	Stainless steel markers, Conductor and cable markers, 131 x 10 mm, silver
Order No.	1912150000
Type	WSMC 21-25
GTIN (EAN)	4032248541195
Qty.	1 Stück

WSMC 21-25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.02 inch
Height	131 mm	Height (inches)	5.157 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	3 g		

Temperatures

Operating temperature range	500 °C
-----------------------------	--------

General data

Colour	silver	Material	Stainless steel 1.4404
Number of characters	25	Number of markers per combination	1 Component part = Conductor and cable markers
Operating temperature range	500 °C	Operating temperature range, max.	500 °C
Orientation of print	horizontal	Printed characters	Mixed characters
Type of printing	To customer specification	Width	10 mm

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format