

WKS 2/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

General ordering data

Version	Accessories, Cross-connection slider, x 77.3
Order No.	1936 180000
Type	WKS 2/10
GTIN (EAN)	4032248605910
Qty.	20 pc(s).

Creation date March 3, 2023 11:51:39 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

WKS 2/10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	16.1 mm	Depth (inches)	0.634 inch
Height	18.86 mm	Height (inches)	0.743 inch
Width	77.3 mm	Width (inches)	3.043 inch
Net weight	9.3 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Polyamide 66	Colour	orange
UL 94 flammability rating	V-2		

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	Plugged
Type of mounting	Clamped		

Dimensions

Pitch in mm (P)	7.9 mm
-----------------	--------

General

Installation advice	Direct mounting	Number of poles	10
Operating temperature range, max.	100 °C		

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
