

**IE-BI-SCRJ2SC-SM-C****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



FO SC inserts for plug-in connectors ver.1 / 4 / 14

**General ordering data**

Version	SC insert, Bulkhead insert SCRJ to 2 SC, singlemode
Order No.	<a href="#">1962870000</a>
Type	IE-BI-SCRJ2SC-SM-C
GTIN (EAN)	4032248645060
Qty.	10 Stück

## IE-BI-SCRJ2SC-SM-C

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	34 mm	Depth (inches)	1.339 inch
Height	13.2 mm	Height (inches)	0.52 inch
Width	15.6 mm	Width (inches)	0.614 inch
Net weight	1.1 g		

### Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

### General data

Colour	Miscellaneous	Configuration	Connector and flange insert for variant 1, 4 and 14 housings
Connection 1	SC	Connection 2	SCRJ
Description of article	Bulkhead insert SCRJ to 2 SC, singlemode	Fibre type	Singlemode
Housing main material	PA	Insertion loss	≤ 0.5 dB
Plugging cycles	1000	Protection degree	IP67 with housing
Return loss (attenuation)	≥ 40 dB		

### General standards

Connector standard	IEC 61754-4, IEC 61754-24
--------------------	---------------------------

### Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

### Approvals

ROHS	Conform
------	---------

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">GOST Approval</a> <a href="#">PROFINET Manufacturer's Declaration</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a> <a href="#">Designation key / Type key</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

## IE-BI-SCRJ2SC-SM-C

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Zeichnungen

### Dimensioned drawing

