

IE-PS-SCRJ-MM**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



FO SC-RJ plug-in connectors according to IEC 61754-24
for wire outer diameters 2.6 to 3 mm

General ordering data

Version	FO connector, Plug SCRJ, multimode, IP20
Order No.	1962940000
Type	IE-PS-SCRJ-MM
GTIN (EAN)	4032248653997
Qty.	10 Stück

IE-PS-SCRJ-MM

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	18.6 g	www.weidmueller.com
------------	--------	---------------------

Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

General data

Colour	Miscellaneous	Connection 1	SCRJ
Connection 2	gluing, crimping, polishing	Description of article	Plug SCRJ, multimode
Ferrule material	Zirconia	Fibre type	Multimode
Insertion loss	≤ 0.4 dB	Plugging cycles	1000
Protection degree	IP20	Return loss (attenuation)	≥ 30 dB

General standards

Connector standard	IEC 61754-24
--------------------	--------------

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	4f3aae94-c2bc-4010-b63b-5b114ba6bd55

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	GOST Approval
Engineering Data	WSCAD
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN