

IE-PS-V01M-2SC-MM**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Bayonet plug-in connector sets according to IEC
61076-3-106 ver.1 (EtherNet/IP), RJ45 metal insert incl.
SC insert

General ordering data

Version	FO connector, Variant 1, SC-Duplex multi-mode, IP67
Order No.	1963260000
Type	IE-PS-V01M-2SC-MM
GTIN (EAN)	4032248651733
Qty.	10 Stück

IE-PS-V01M-2SC-MM

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	87 mm	Depth (inches)	3.425 inch
Height	30 mm	Height (inches)	1.181 inch
Width	30 mm	Width (inches)	1.181 inch
Net weight	11.2 g		

Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

General data

Colour	Miscellaneous	Connection 1	SCRJ
Connection 2	gluing, crimping, polishing	Description of article	Variant 1, SC-Duplex multimode
Fibre type	Multimode	Housing main material	Zinc diecast
Housing material, insert	PA, Zinc diecast	Insertion loss	0.5 dB singlemode; 0.4 dB multimode; 1.5 dB POF
Plugging cycles	500	Protection degree	IP67
Return loss (attenuation)	40 dB singlemode; 30 dB multimode	Sheath diameter, max.	10 mm
Sheath diameter, min.	5 mm		

General standards

Connector standard	IEC 61076-3-106 Var. 1, IEC 61754-24
--------------------	--------------------------------------


Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	e5bbf197-73b5-420b-90c0-0173b7b3b6b7

Approvals

Approvals	
ROHS	Conform

IE-PS-V01M-2SC-MM

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Downloads

Approval/Certificate/Document of
Conformity

[GOST Approval](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD](#)

User Documentation

[MAN IE GUIDE DE](#)

[MAN IE GUIDE EN](#)

[Designation key / Type key](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)

[PI PROFINET CABLING EN](#)

[PI PROFINET CABLING EN](#)

IE-PS-V01M-2SC-MM

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

Dimensioned drawing

