

## IE-PP-V01P

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



For protecting your devices against dust and dirt.

### General ordering data

Version	Plug housing protective cap
Order No.	<a href="#">1965690000</a>
Type	IE-PP-V01P
GTIN (EAN)	4032248653911
Qty.	10 Stück

Erstellungs-Datum May 30, 2023 5:29:18 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## IE-PP-V01P

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	35.2 mm	Depth (inches)	1.386 inch
Net weight	11.716 g		

### Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

### General data

Colour	black	Housing main material	PA UL 94 V0
Protection degree	IP67	Type of mounting	Indoors only
UL 94 flammability rating	V-0		

### Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ECLASS 9.0	27-44-02-08
ECLASS 9.1	27-44-02-08	ECLASS 10.0	27-44-02-08
ECLASS 11.0	27-44-02-08	ECLASS 12.0	27-44-02-08

### Approvals

Approvals



ROHS Conform

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">UL Approval</a> <a href="#">GOST Approval</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>