

IE-BP-V01P**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



For protecting your devices against dust and dirt.

General ordering data

Version	Flange-mounted housing, protective cap
Order No.	1965700000
Type	IE-BP-V01P
GTIN (EAN)	4032248653928
Qty.	10 Stück

IE-BP-V01P

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	22.7 mm	Depth (inches)	0.894 inch
Net weight	7.446 g		

Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

General data

Colour	black	Housing main material	PA UL 94 V0
Protection degree	IP67	Type of mounting	Indoors only
UL 94 flammability rating	V-0		

Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ECLASS 9.0	27-44-02-08
ECLASS 9.1	27-44-02-08	ECLASS 10.0	27-44-02-08
ECLASS 11.0	27-44-02-08	ECLASS 12.0	27-44-02-08

Environmental Product Compliance

REACH SVHC	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	11b17e97-f803-4c09-9278-b20f22f15f81

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	UL Approval GOST Approval
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN