

DGSB IP30 D0 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Intelligent cabling solutions can save you valuable time and money.**

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread

Integration of operating and signalling devices into the seal possible

General ordering data

| | |
|------------|--|
| Version | Field Power® sealing insert, Blank seal, IP30, with corresponding enclosure, TPE-U |
| Order No. | 1967600000 |
| Type | DGSB IP30 D0 PT6 |
| GTIN (EAN) | 4032248688746 |
| Qty. | 10 pc(s). |

Creation date March 9, 2023 2:01:44 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

DGSB IP30 D0 PT6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 3.15 mm | Depth (inches) | 0.124 inch |
| Height | 23.51 mm | Height (inches) | 0.926 inch |
| Width | 35 mm | Width (inches) | 1.378 inch |
| Net weight | 1.6 g | | |

Temperatures

| | | | |
|-----------------------------|----------------|-----------------------------|----------------|
| Storage temperature | -40 °C...55 °C | Operating temperature | -40 °C...55 °C |
| Operating temperature, min. | -40 °C | Operating temperature, max. | 55 °C |

General data

| | | | |
|-------------------|------------------------------------|--|----------------------------------|
| Colour | grey | Design | Blank seal |
| Material | TPE-U | Mounting position, installation notice | in FieldPower® IP30 sealing slot |
| Protection degree | IP30, with corresponding enclosure | Silicone | No |

General data

| | | | |
|----------|-------|-------------------|------------------------------------|
| Material | TPE-U | Protection degree | IP30, with corresponding enclosure |
| Silicone | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002624 | ETIM 7.0 | EC002624 |
| ETIM 8.0 | EC002624 | ECLASS 9.1 | 27-18-27-90 |
| ECLASS 10.0 | 27-18-28-15 | ECLASS 11.0 | 27-18-28-15 |
| ECLASS 12.0 | 27-18-28-15 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | Manufacturer's Declaration FieldPower® BOX, BOX FUSE and Terminal variants |
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |