

ZQV 1.5N/8**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Order No.	1985540000
Type	ZQV 1.5N/8
GTIN (EAN)	4050118370218
Qty.	20 pc(s).

ZQV 1.5N/8

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	2.8 mm	Depth (inches)	0.11 inch
Height	21.9 mm	Height (inches)	0.862 inch
Width	26.5 mm	Width (inches)	1.043 inch
Net weight	2.511 g		

Temperatures

Storage temperature -25 °C...55 °C

Material data

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version Yes Type of fixing Plugged

Cross-connector

Rated current, 2-pole 17.5 A Rated current, multi-pole 17.5 A

Dimensions

Pitch in mm (P) 3.5 mm

General

Number of poles 8

Rating data

Rated current 17.5 A

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Important note

Product information Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400V The voltage reduced to 25V if cut cross connection with blank cut edges are used

ZQV 1.5N/8**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com**Technical data**www.weidmueller.com**Downloads**

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	2434520000_BED-ANL_ZQV_A_REIHE.pdf StorageConditionsTerminalBlocks BPZL ZQV 2.5
Catalogues	Catalogues in PDF-format
Brochures	