

IE-USB-A-A-1.8M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	USB cable, USB A, USB A, PVC, 1.8 m
Order No.	1993550018
Type	IE-USB-A-A-1.8M
GTIN (EAN)	4050118378641
Qty.	1 Stück

Erstellungs-Datum June 2, 2023 9:37:17 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

IE-USB-A-A-1.8M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Length	1.8 m	Length (inches)	70.866 inch
Net weight	53 g		

Temperatures

Operating temperature	-15 °C...80 °C	Operating temperature, min.	-15 °C
Operating temperature, max.	80 °C		

Technical specifications for cable

Sheathing colour	black
------------------	-------

General technical data

Contact surface	Gold over nickel
-----------------	------------------

Cable structure

Cross-section	2*AWG28 + 2*AWG24	Material sheath	PVC
Sheath diameter	4.5 mm	Sheath diameter, max.	4.7 mm
Sheath diameter, min.	4.3 mm	Sheathing colour	black

Plug

Plug	Cable side	left	
	Version of contact face	USB A	
	Protection degree (IP)	IP20	
	Gender of contact	male contact	
	Outlet direction	straight	
	Version of connector	plug	
	Housing main material	Plastic	
	Status indicator available	No	
	Shielding available	Yes	
	Cable side	right	
	Version of contact face	USB A	
	Protection degree (IP)	IP20	
	Gender of contact	male contact	
	Outlet direction	straight	
	Version of connector	plug	
	Housing main material	Plastic	
	Status indicator available	No	
	Shielding available	Yes	
	Plug left	USB A, IP20, male contact, straight, plug, Plastic, shielded	
	Plug right	USB A, IP20, male contact, straight, plug, Plastic, shielded	

Plug, left

Connector left	USB A	Contact surface, plug, left	Gold over nickel
Plug left	USB A, IP20, male contact, straight, plug, Plastic, shielded		

IE-USB-A-A-1.8M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Plug, right

Connector right	USB A	Contact surface	Gold over nickel
Plug right	USB A, IP20, male contact, straight, plug, Plastic, shielded		

Classifications

ETIM 6.0	EC001408	ETIM 7.0	EC001408
ETIM 8.0	EC001408	ECLASS 9.0	27-06-20-11
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-01-06
ECLASS 11.0	27-06-01-06	ECLASS 12.0	27-06-01-06

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN