

ES EPG 45 WM 150

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

General ordering data

Version	WM crimp
Order No.	1994550000
Type	ES EPG 45 WM 150
GTIN (EAN)	4050118379785
Qty.	1 Stück

ES EPG 45 WM 150

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	12 mm	Depth (inches)	0.472 inch
Height	60 mm	Height (inches)	2.362 inch
Width	30 mm	Width (inches)	1.181 inch
Net weight	2.75 g		

Crimp inserts

Crimp cross-section copper	150	Crimping width	5 mm
Crimping width in mm	5		

Description of contact

Conductor cross-section, max. AWG	5/0
-----------------------------------	-----

tool data crimping

Cable lug cross section	nominal	150 mm ²
Crimping type/profile	WM crimp	

Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Downloads

Catalogues	Catalogues in PDF-format
------------	--