

**SFX 11/60 MM GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



**Highly flexible: SFX**

SFX markers are the preferred choice for labelling cables if you prefer the classic cable tie solution. Cables do not always run in a straight line. The material used in SFX markers addresses this fact with highly flexible polyurethane. The marker follows each curve of the cable and latches on with ease.

**General ordering data**

|                    |  |
|--------------------|--|
| Version            | SlimFix, Conductor and cable markers, 7 - , 60 x 13 mm, yellow |
| Order No.          | <a href="#">2005400000</a>                                     |
| Type               | SFX 11/60 MM GE  |
| GTIN (EAN)         | 4050118390209  |
| Qty.               | 1,000 Stück  |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a>          |

Erstellungs-Datum May 22, 2023 1:19:24 PM CEST

## SFX 11/60 MM GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.6 mm  | Depth (inches)  | 0.024 inch |
| Height     | 60 mm   | Height (inches) | 2.362 inch |
| Width      | 13 mm   | Width (inches)  | 0.512 inch |
| Net weight | 0.566 g |                 |            |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -40...90 °C |
|-----------------------------|-------------|

### General data

|                                   |              |                                   |              |
|-----------------------------------|--------------|-----------------------------------|--------------|
| Colour                            | yellow       | Halogen                           | No           |
| Material                          | Polyurethane | Number per roll                   | 1,000        |
| Operating temperature range       | -40...90 °C  | Operating temperature range, max. | 90 °C        |
| Operating temperature range, min. | -40 °C       | Size of labelling field           | 44 x 10.5 mm |
| UL 94 flammability rating         | HB           | Version                           | halogen-free |
| Width                             | 13 mm        |                                   |              |

### Conductor and cable markers

|                      |         |                   |         |
|----------------------|---------|-------------------|---------|
| Cable tie passage    | Flat    | Conductor O.D.    | 7 -     |
| Conductor O.D., min. | 7 mm    | Halogen           | No      |
| Suitable cable tie   | Plastic | Text field height | 10.5 mm |
| Text field width     | 44 mm   |                   |         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">WSCAD, Zuken E3.S, EPLAN</a> |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

**Datenblatt**

**SFX 11/60 MM GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

