

TM-I 20 MM BL

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Process reliability: TM-I**

TM-I inlay tags have a guide tab which allows them to slide easily into the transparent sleeves from the type TM. Once the tag is in place, the tab is snapped off at the predetermined break point. The ready-assembled sleeves can then be simply pushed over the conductors. Your benefits: large quantities can be efficiently pre-assembled in a single step.

General ordering data

| | |
|--------------------|---|
| Version | TM-I, Insert markers, 20 x 4 mm, blue |
| Order No. | 2005950000 |
| Type | TM-I 20 MM BL |
| GTIN (EAN) | 4050118390490 |
| Qty. | 2,000 Stück |
| compatible printer | 2599430000 2599440000 |

TM-I 20 MM BL

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Height | 20 mm | Height (inches) | 0.787 inch |
| Width | 4 mm | Width (inches) | 0.157 inch |
| Net weight | 0.186 g | | |

Temperatures

| | | | |
|-----------------------------|--------------|-----------------------------|--------|
| Operating temperature range | -40...150 °C | Operating temperature, min. | -40 °C |
| Operating temperature, max. | 150 °C | | |

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|-------------------------|
| Colour | blue | Halogen | No |
| Material | Polyester | Number per roll | 2,000 |
| Operating temperature range | -40...150 °C | Operating temperature range, max. | 150 °C |
| Operating temperature range, min. | -40 °C | Orientation of print | horizontal and vertical |
| Printed characters | without | Type of printing | neutral |
| UL 94 flammability rating | HB | Width | 4 mm |

Conductor and cable markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S, EPLAN |
| Catalogues | Catalogues in PDF-format |

TM-I 20 MM BL

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

