

## KTB GP 624520 CD S4 PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Similar to illustration



Abbildung ähnlich

### **Integrate, expand and customise: The ideal expansion for every application**

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

#### **Flange plates**

Flange plates in two thicknesses, for easy replacement of pre-assembl

### General ordering data

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 564 mm, Width: 167 mm, Depth: 3 mm, Gland plates: left, right, Material: Stainless steel 1.4404, electropolished, silver
Order No.	<a href="#">2023930000</a>
Type	KTB GP 624520 CD S4 PE
GTIN (EAN)	4050118404319
Qty.	1 Stück

Erstellungs-Datum May 25, 2023 1:20:38 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## KTB GP 624520 CD S4 PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	3 mm	Depth (inches)	0.118 inch
Height	564 mm	Height (inches)	22.205 inch
Width	167 mm	Width (inches)	6.575 inch
Net weight	2,230 g		

### General information

Gland plates	left, right	Material	Stainless steel 1.4404
Material thickness	3 mm	Protection class (UL)	Type 3, Type 4X, Type 12
Surface finish	electropolished		

### General information on accessories

Material	Stainless steel 1.4404	Material thickness	3 mm
Surface finish	electropolished		

### Housing earth

Flange plate earthing	M6 x 15
-----------------------	---------

### Classifications

ETIM 6.0	EC000211	ETIM 7.0	EC000211
ETIM 8.0	EC000211	ECLASS 9.0	27-14-24-21
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-14-24-21
ECLASS 11.0	27-14-24-21	ECLASS 12.0	27-14-24-21

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	