

**VP M16 EX SI 7J****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Similar to illustration**

For sealing surplus threaded holes to maintain the IP class of protection

**General ordering data**

Version	VPK EX 7J (Ex blanking plug, plastic, 7J), Blanking plug, in closed state, M 16, 12 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	<a href="#">2066720000</a>
Type	VP M16 EX SI 7J
GTIN (EAN)	4050118415438
Qty.	100 Stück

## VP M16 EX SI 7J

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

Height	16.3 mm	Height (inches)	0.642 inch
Length	16.3 mm	Length (inches)	0.642 inch
Diameter	16 mm	Wall thickness, max.	11 mm
Net weight	2.3 g		

### Temperatures

Operating temperature	-60 °C...70 °C	Operating temperature, min.	-60 °C
Operating temperature, max.	70 °C		

### Technical properties

Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
-------------------	--

### Technical data

Colour	Deep black	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
--------	------------	-------------------	--

### Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-35	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25	ECLASS 12.0	27-14-08-05

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	