

PAC-HE16-HE16-HF-1M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

Version	
Order No.	2425700010
Type	PAC-HE16-HE16-HF-1M
GTIN (EAN)	4032248273287
Qty.	1 pc(s).

Creation date March 17, 2023 12:11:32 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

PAC-HE16-HE16-HF-1M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 80.3 g

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
Operating temperature, min.	-10 °C	Operating temperature, max.	50 °C

General Data

Cable	Cable LIHH	Cable length	1 m
Connector PLC side	FLAT CABLE CONNECTOR HE10 16P	Interface connector	FLAT CABLE CONNECTOR HE10 16P
Number of poles, min.	16-pole	Suitable for	Digital signals
Wire cross-section	0.14 mm ²		

Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 V DC ≤ 25 V AC	Resistance	≤ 150mΩ/m
Total current, max.	3 A		

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20

Approvals

ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)