

**PAC-D15M-D15M-HF-1M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

Version	
Order No.	<a href="#">2426070010</a>
Type	PAC-D15M-D15M-HF-1M
GTIN (EAN)	4032248274239
Qty.	1 pc(s).

## PAC-D15M-D15M-HF-1M

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Net weight 227 g

### Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
Operating temperature, min.	-10 °C	Operating temperature, max.	50 °C

### General Data

Cable	Cable LIHCH	Cable length	1 m
Connector PLC side	SUB-D MALE 15P	Interface connector	SUB-D MALE 15P
Number of poles, min.	15-pole	Suitable for	Analogue signals
Wire cross-section	0.25 mm <sup>2</sup>		

### Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 Vdc ≤ 25 Vac	Resistance	≤ 80 mΩ/m
Total current, max.	3 A		

### Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	4bbf2c0d-0764-4fc8-bb24-9351c28c190d

### Approvals

ROHS	Conform
------	---------

### Downloads

Catalogues [Catalogues in PDF-format](#)