

VT M

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



- Reacts from a distance of 4 mm
- for testing operation of solenoid valves, relays, coils and contactors
- all magnetic fields can be tested
- Visual indication
- including a flashlight function with the Testboy 120

General ordering data

Version	Testing tools, Non-contact magnetic field tester
Order No.	2436680000
Type	VT M
GTIN (EAN)	4050118450019
Qty.	1 Stück

VT M

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 55.7 g

Technical data

Description of article Non-contact magnetic field tester

Measuring and testing devices

Battery type	1.5 V type AAA battery	Display	Visual & acoustic
Protection degree	IP65	Tested and approved according to	DIN EN 61010-1, DIN EN 61326

Classifications

ETIM 6.0	EC000494	ETIM 7.0	EC000494
ETIM 8.0	EC000494	ECLASS 9.0	27-20-03-08
ECLASS 9.1	27-20-03-08	ECLASS 10.0	27-20-03-08
ECLASS 11.0	27-20-03-08	ECLASS 12.0	27-20-03-08

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

Approvals



ROHS Conform

Downloads

User Documentation [Manual](#)
 Catalogues [Catalogues in PDF-format](#)