

KCMA-18-50-1A-1VA-3 HUT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image, Similar to illustration**Cable-type current transformer**

The cable-type current transformer is mainly used for retrofitting in order to avoid cutting the primary conductors.

Due to its dimensions and the convenient handling, the cable-type current transformer is particularly suitable for use in places that are difficult to access or where space is limited.

The "click" system in conjunction with the fixing clamps even makes "one-handed" installation possible.

General ordering data

Version	Primary current: 50 A, Secondary current max.: 1 A, Load: 1 VA, Tolerance class: 3, Split-core current transformer
Order No.	2511690000
Type	KCMA-18-50-1A-1VA-3 HUT
GTIN (EAN)	4050118527643
Qty.	1 Stück

Erstellungs-Datum June 2, 2023 10:45:39 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

KCMA-18-50-1A-1VA-3 HUT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	264 g
------------	-------

Temperatures

Storage temperature	-25 °C...70 °C	Operating temperature	-5 °C...50 °C
Operating temperature, min.	-5 °C	Operating temperature, max.	50 °C

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	18.5 mm
Installation location	Indoor use		

Electrical attributes

Load	1 VA	Primary current	50 A
Secondary current max.	1 A	Tolerance class	3

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ECLASS 9.0	27-21-09-02
ECLASS 9.1	27-21-09-02	ECLASS 10.0	27-21-09-02
ECLASS 11.0	27-21-09-02	ECLASS 12.0	27-21-09-02

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Instruction sheet German
Catalogues	Catalogues in PDF-format

KCMA-18-50-1A-1VA-3 HUT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

