

CD-SE 100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Version	Cable duct separator, 100 mm x
Order No.	2553990000
Type	CD-SE 100
GTIN (EAN)	4050118564129
Qty.	32 Stück

CD-SE 100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	100 mm	Height (inches)	3.937 inch
Length	1,000 mm	Length (inches)	39.37 inch
Net weight	253 g		

Temperatures

Operating temperature range	-5...60 °C	Operating temperature, min.	-5 °C
Operating temperature, max.	60 °C		

General information

Colour	grey	Material	PVC
Non-tracking	Yes	Operating temperature range	-5...60 °C
UL 94 flammability rating	V-0	Version	1-wall

Classifications

ETIM 6.0	EC001015	ETIM 7.0	EC001015
ETIM 8.0	EC001015	ECLASS 9.1	27-40-07-52
ECLASS 10.0	27-40-07-52	ECLASS 11.0	27-40-07-52
ECLASS 12.0	27-40-07-52		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--