

## CD-RET 125

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

### General ordering data

Version	Cable duct binder
Order No.	<a href="#">2554070000</a>
Type	CD-RET 125
GTIN (EAN)	4050118564198
Qty.	200 Stück

## CD-RET 125

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 5 g

### Temperatures

Operating temperature range	-40...100 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	100 °C		

### General information

Channel width	125	Colour	yellow
Material	Polyamide 6 (PA 6)	Non-tracking	Yes
Operating temperature range	-40...100 °C	UL 94 flammability rating	HB
Usage	For 125 mm wiring ducts		

### Classifications

ETIM 6.0	EC001018	ETIM 7.0	EC001018
ETIM 8.0	EC001018	ECLASS 9.0	27-40-07-65
ECLASS 9.1	27-40-07-65	ECLASS 10.0	27-40-07-65
ECLASS 11.0	27-40-07-65	ECLASS 12.0	27-40-07-65

### Approvals

ROHS Conform

### Downloads

Catalogues [Catalogues in PDF-format](#)