

CD-RETA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Version	Cable duct binder arm
Order No.	2554080000
Type	CD-RETA
GTIN (EAN)	4050118564204
Qty.	100 Stück

CD-RETA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 3 g

Temperatures

Operating temperature range	-40...100 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	100 °C		

General information

Channel width	40-120	Colour	yellow
Material	Polyamide 6 (PA 6)	Non-tracking	Yes
Operating temperature range	-40...100 °C	UL 94 flammability rating	HB
Usage	For all wiring ducts (up to max. 105 mm wide)		

Classifications

ETIM 6.0	EC001018	ETIM 7.0	EC001018
ETIM 8.0	EC001018	ECLASS 9.0	27-40-07-65
ECLASS 9.1	27-40-07-65	ECLASS 10.0	27-40-07-65
ECLASS 11.0	27-40-07-65	ECLASS 12.0	27-40-07-65

Approvals

ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)