

TCC 12.8/26 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Adjustable cross-connections**

Increase the flexibility of your cross-connections. The TERMSERIES CROSS-CONNECTION (TCC) enables individually adjustable cross-connections with up to 51 poles. The maximum number of pluggable poles has been increased to 32 poles. The strip material can be shortened to the required length very easily. The cross-connectors convince thanks to their easy handling and visibility as well as their universal connection possibilities. An additional web prevents the spring from deforming during assembly.

- Individually adjustable cross-connection with 51 poles
- Additional bar to avoid deformation of the spring
- Increased cross-connection – up to 32 poles possible
- Vibration resistance

General ordering data

Version	TERMSERIES, Cross-connector
Order No.	2556460000
Type	TCC 12.8/26 BL
GTIN (EAN)	4050118566970
Qty.	10 Stück

TCC 12.8/26 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	4.8 mm	Depth (inches)	0.189 inch
Height	13.1 mm	Height (inches)	0.516 inch
Width	323.4 mm	Width (inches)	12.732 inch
Net weight	9.7 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...60 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	60 °C

Cross-connection data

Rated voltage	300 V	Rated current	17.5 A
Insulation	Yes	Touch-safe protection	Yes
Colour	blue	Number of cross-connected terminals	16
Number of poles	26	Pitch in mm (P)	12.8 mm
Type of mounting	Plugged	Version	can be cut to length

Rated data UL

Rated current (UL)	10 A
--------------------	------

General data

Version	can be cut to length		
Colour	blue		
UL94 flammability rating component	Component	Housing	
	UL94 flammability rating	V-0	

Insulation coordination

Rated voltage	300 V
---------------	-------

Connection data

Pitch in mm (P)	12.8 mm
-----------------	---------

Classifications

ETIM 6.0	EC002586	ETIM 7.0	EC002586
ETIM 8.0	EC002586	ECLASS 9.1	27-37-16-92
ECLASS 10.0	27-37-16-92	ECLASS 11.0	27-37-16-92
ECLASS 12.0	27-37-16-92		

Approvals

Approvals



ROHS

Conform

TCC 12.8/26 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN
User Documentation	Beipackzettel / Package Insert Beipackzettel / Package Insert – multilingual
Catalogues	Catalogues in PDF-format


TCC 12.8/26 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Zeichnungen

Product image




Dimensional drawing



Miscellaneous

Type code TERMSERIES accessories



Type codes