

RFF 605 33/230V GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Ideal for indoor use in tight spaces. Optimised air flow and temperature distribution, protection according to IP33 or IP54 and high UV resistance.

General ordering data

Version	Filter fan, IP33, grey
Order No.	2557740000
Type	RFF 605 33/230V GY
GTIN (EAN)	4050118568387
Qty.	1 Stück

RFF 605 33/230V GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	106 mm	Depth (inches)	4.173 inch
Height	436 mm	Height (inches)	17.165 inch
Width	436 mm	Width (inches)	17.165 inch
Net weight	3,240 g		

Temperatures

Operating temperature range	-15...55 °C
-----------------------------	-------------

General data

Colour	grey		
Current consumption	Mains frequency	50 Hz	
	Current	0.8 A	
	Mains frequency	60 Hz	
	Current	0.8 A	
EMC version	No		
Fan type	Roof fan		
Fuse	6 A		
Height of installation cut-outs	291 mm		
MTBF	50,000 h		
Mounting depth	34 mm		
Mounting height	72 mm		
Noise emission	67 dB(A)		
Operating temperature range	-15...55 °C		
Power	Mains frequency	50 Hz	
	nominal	112 W	
	Mains frequency	60 Hz	
	nominal	116 W	
Rated voltage	230 V AC ± 10%		
Type of connection	Terminal strip		
Type of mounting	Snap-on		
Volume flow with exhaust filter	Mains frequency	50 Hz	
	Volume flow	268 m³/h	
	Exhaust filter	IP33	
	Mains frequency	60 Hz	
	Volume flow	268 m³/h	
Volume flow, free-blowing	Exhaust filter	IP33	
	Mains frequency	50 Hz	
	Volume flow	500 m³/h	
	Mains frequency	60 Hz	
Volume flow, free-blowing at 50 Hz	Volume flow	500 m³/h	
	Mains frequency	60 Hz	
Volume flow, free-blowing at 60 Hz	500 m³/h		
Width of installation cut-outs	291 mm		
With filter	No		

Classifications

ETIM 6.0	EC000320	ETIM 7.0	EC000320
ETIM 8.0	EC000320	ECLASS 9.1	27-18-07-16
ECLASS 10.0	27-18-07-16	ECLASS 11.0	27-18-07-16
ECLASS 12.0	27-18-07-16		

Erstellungs-Datum June 1, 2023 9:25:57 AM CEST

RFF 605 33/230V GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E252704

Downloads

Approval/Certificate/Document of Conformity [EU Declaration of Conformity](#)

User Documentation [Installation- and operating instructions](#)

Catalogues [Catalogues in PDF-format](#)