

**RFF 607 33/230V GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

Ideal for indoor use in tight spaces. Optimised air flow and temperature distribution, protection according to IP33 or IP54 and high UV resistance.

**General ordering data**

Version	Filter fan, IP33, grey
Order No.	<a href="#">2557780000</a>
Type	RFF 607 33/230V GY
GTIN (EAN)	4050118568424
Qty.	1 Stück

## RFF 607 33/230V GY

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	152 mm	Depth (inches)	5.984 inch
Height	470 mm	Height (inches)	18.504 inch
Width	470 mm	Width (inches)	18.504 inch
Net weight	4,100 g		

### Temperatures

Operating temperature range	-15...55 °C
-----------------------------	-------------

### General data

Colour	grey		
Current consumption	Mains frequency	50 Hz	
	Current	0.35 A	
	Mains frequency	60 Hz	
	Current	0.45 A	
EMC version	No		
Fan type	Roof fan		
Fuse	6 A		
Height of installation cut-outs	291 mm		
MTBF	40,000 h		
Mounting depth	57 mm		
Mounting height	95 mm		
Noise emission	69 dB(A)		
Operating temperature range	-15...55 °C		
Power	Mains frequency	50 Hz	
	nominal	80 W	
	Mains frequency	60 Hz	
	nominal	100 W	
Rated voltage	230 V AC ± 10%		
Type of connection	Terminal strip		
Type of mounting	Snap-on		
Volume flow with exhaust filter	Mains frequency	50 Hz	
	Volume flow	427 m³/h	
	Exhaust filter	IP33	
	Mains frequency	60 Hz	
	Volume flow	427 m³/h	
Volume flow, free-blowing	Exhaust filter	IP33	
	Mains frequency	50 Hz	
	Volume flow	700 m³/h	
	Mains frequency	60 Hz	
	Volume flow	700 m³/h	
Volume flow, free-blowing at 50 Hz	700 m³/h		
Volume flow, free-blowing at 60 Hz	700 m³/h		
Width of installation cut-outs	291 mm		
With filter	No		

### Classifications

ETIM 6.0	EC000320	ETIM 7.0	EC000320
ETIM 8.0	EC000320	ECLASS 9.1	27-18-07-16
ECLASS 10.0	27-18-07-16	ECLASS 11.0	27-18-07-16
ECLASS 12.0	27-18-07-16		

Erstellungs-Datum June 1, 2023 9:26:25 AM CEST

**RFF 607 33/230V GY**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E252704

### Downloads

Approval/Certificate/Document of Conformity [EU Declaration of Conformity](#)

User Documentation [Installation- and operating instructions](#)

Catalogues [Catalogues in PDF-format](#)