

**RH-CBCO 30W 110-250V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

**General ordering data**

Version	Radiant heating panel, 110 V, 250 V, IP44, silver
Order No.	<a href="#">2557890000</a>
Type	RH-CBCO 30W 110-250V
GTIN (EAN)	4050118568530
Qty.	1 Stück

## RH-CBCO 30W 110-250V

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	50 mm	Depth (inches)	1.969 inch
Height	100 mm	Height (inches)	3.937 inch
Width	70 mm	Width (inches)	2.756 inch
Net weight	250 g		

### Temperatures

Operating temperature range	-40...70 °C
-----------------------------	-------------

### General data

Continuous heat output at 10°C	30 W	Inrush current	max. 1.2 A
Operating temperature range	-40...70 °C	Protection degree	IP44
Supply voltage, max.	250 V	Supply voltage, min.	110 V
Type of connection	Pre-assembled cable	Type of mounting	Rail
With room thermostat	No		

### Classifications

ETIM 6.0	EC000737	ETIM 7.0	EC000737
ETIM 8.0	EC000737	ECLASS 9.1	27-18-07-10
ECLASS 10.0	27-18-07-10	ECLASS 11.0	27-18-07-10
ECLASS 12.0	27-18-07-10		

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E497839

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>