

RH-CBCO 100W 110-250V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

General ordering data

Version	Radiant heating panel, 110 V, 250 V, IP44, silver
Order No.	2557940000
Type	RH-CBCO 100W 110-250V
GTIN (EAN)	4050118568585
Qty.	1 Stück

RH-CBCO 100W 110-250V

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	50 mm	Depth (inches)	1.969 inch
Height	175 mm	Height (inches)	6.89 inch
Width	70 mm	Width (inches)	2.756 inch
Net weight	510 g		

Temperatures

Operating temperature range	-40...70 °C
-----------------------------	-------------

General data

Continuous heat output at 10°C	100 W	Inrush current	max. 5 A
Operating temperature range	-40...70 °C	Protection degree	IP44
Supply voltage, max.	250 V	Supply voltage, min.	110 V
Type of connection	Pre-assembled cable	Type of mounting	Rail
With room thermostat	No		

Classifications

ETIM 6.0	EC000737	ETIM 7.0	EC000737
ETIM 8.0	EC000737	ECLASS 9.1	27-18-07-10
ECLASS 10.0	27-18-07-10	ECLASS 11.0	27-18-07-10
ECLASS 12.0	27-18-07-10		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E497839

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format