

FH-TCO 400W 230V**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

General ordering data

Version	Heating panel fan, IP20, silver
Order No.	2558000000
Type	FH-TCO 400W 230V
GTIN (EAN)	4050118568646
Qty.	1 Stück

FH-TCO 400W 230V

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	104 mm	Depth (inches)	4.094 inch
Height	226.5 mm	Height (inches)	8.917 inch
Width	85 mm	Width (inches)	3.346 inch
Net weight	1,200 g		

Temperatures

Operating temperature range	-40...70 °C
-----------------------------	-------------

General data

Continuous heat output at 10°C	400 W	Inrush current	max. 1.8 A
Operating temperature range	-40...70 °C	Operating voltage	230 V AC
Protection degree	IP20	Type of connection	Spring contact
Type of mounting	Rail	With room thermostat	No

Classifications

ETIM 6.0	EC000737	ETIM 7.0	EC000737
ETIM 8.0	EC000737	ECLASS 9.1	27-18-07-10
ECLASS 10.0	27-18-07-10	ECLASS 11.0	27-18-07-10
ECLASS 12.0	27-18-07-10		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E497839

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format