

**FH-TCO 200W 230V BK****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

**General ordering data**

Version	Heating panel fan, IP20, black
Order No.	<a href="#">2558010000</a>
Type	FH-TCO 200W 230V BK
GTIN (EAN)	4050118568653
Qty.	1 Stück

## FH-TCO 200W 230V BK

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	126 mm	Depth (inches)	4.961 inch
Height	142 mm	Height (inches)	5.591 inch
Width	88 mm	Width (inches)	3.465 inch
Net weight	740 g		

### Temperatures

Operating temperature range	-40...70 °C
-----------------------------	-------------

### General data

Continuous heat output at 10°C	200 W	Inrush current	max. 9 A
Operating temperature range	-40...70 °C	Operating voltage	230 V AC
Protection degree	IP20	Type of connection	Spring contact
Type of mounting	Rail, Screw mounting	With room thermostat	No

### Classifications

ETIM 6.0	EC000737	ETIM 7.0	EC000737
ETIM 8.0	EC000737	ECLASS 9.1	27-18-07-10
ECLASS 10.0	27-18-07-10	ECLASS 11.0	27-18-07-10
ECLASS 12.0	27-18-07-10		

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E497839

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a> <a href="#">EU Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Operating instructions</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>