

FH-TH 800W 230V BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

General ordering data

Version	Heating panel fan, IP20, black
Order No.	2558 140000
Type	FH-TH 800W 230V BK
GTIN (EAN)	4050 118568790
Qty.	1 Stück

FH-TH 800W 230V BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	139 mm	Depth (inches)	5.472 inch
Height	142 mm	Height (inches)	5.591 inch
Width	88 mm	Width (inches)	3.465 inch
Net weight	800 g		

Temperatures

Operating temperature range	-40...70 °C
-----------------------------	-------------

General data

Continuous heat output at 10°C	800 W	Inrush current	max. 31 A
Operating temperature range	-40...70 °C	Operating voltage	230 V AC
Protection degree	IP20	Temperature setting range, max.	40 °C
Temperature setting range, min.	-20 °C	Type of connection	Spring contact
Type of mounting	Rail, Screw mounting	With room thermostat	Yes

Classifications

ETIM 6.0	EC000737	ETIM 7.0	EC000737
ETIM 8.0	EC000737	ECLASS 9.1	27-18-07-10
ECLASS 10.0	27-18-07-10	ECLASS 11.0	27-18-07-10
ECLASS 12.0	27-18-07-10		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E497839

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity EU Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Operating instructions
Catalogues	Catalogues in PDF-format