

CD-FLEX 12.5X12.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Version	Flexible wiring duct, 12.5 mm x 12.5 mm, 5.00 mm x 7.50 mm, 500 mm
Order No.	2562770000
Type	CD-FLEX 12.5X12.5
GTIN (EAN)	4050118571585
Qty.	50 Stück

CD-FLEX 12.5X12.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	12.5 mm	Height (inches)	0.492 inch
Width	12.5 mm	Width (inches)	0.492 inch
Length	500 mm	Length (inches)	19.685 inch
Net weight	12 g		

Temperatures

Operating temperature range	-15...80 °C	Operating temperature, min.	-15 °C
Operating temperature, max.	80 °C		

General information

Colour	grey (similar to RAL 7001)	Flexible wiring duct	Yes
Lid	No	Material	Polypropylene
Non-tracking	Yes	Operating temperature range	-15...80 °C
Slit gap	7.5 mm	Slit width	5 mm
Type of mounting	With adhesive	UL 94 flammability rating	V-2
Version of side panel	slotted		

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ECLASS 9.1	27-40-07-03
ECLASS 10.0	27-40-07-03	ECLASS 11.0	27-40-07-03
ECLASS 12.0	27-40-07-03		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--