

**CD-FLEX 20X20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

**General ordering data**

|            |  |
|------------|--|
| Version    | Flexible wiring duct, 20 mm x 20 mm, 5.00 mm x 7.50 mm, 500 mm |
| Order No.  | <a href="#">2562780000</a>                                     |
| Type       | CD-FLEX 20X20  |
| GTIN (EAN) | 4050118571554  |
| Qty.       | 50 Stück   |

## CD-FLEX 20X20

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 20 mm  | Height (inches) | 0.787 inch  |
| Width      | 20 mm  | Width (inches)  | 0.787 inch  |
| Length     | 500 mm | Length (inches) | 19.685 inch |
| Net weight | 19 g   |                 |             |

### Temperatures

|                             |             |                             |        |
|-----------------------------|-------------|-----------------------------|--------|
| Operating temperature range | -15...80 °C | Operating temperature, min. | -15 °C |
| Operating temperature, max. | 80 °C       |                             |        |

### General information

|                       |                            |                             |               |
|-----------------------|----------------------------|-----------------------------|---------------|
| Colour                | grey (similar to RAL 7001) | Flexible wiring duct        | Yes           |
| Lid                   | No                         | Material                    | Polypropylene |
| Non-tracking          | Yes                        | Operating temperature range | -15...80 °C   |
| Slit gap              | 7.5 mm                     | Slit width                  | 5 mm          |
| Type of mounting      | With adhesive              | UL 94 flammability rating   | V-2           |
| Version of side panel | slotted                    |                             |               |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000012    | ETIM 7.0    | EC000012    |
| ETIM 8.0    | EC000012    | ECLASS 9.1  | 27-40-07-03 |
| ECLASS 10.0 | 27-40-07-03 | ECLASS 11.0 | 27-40-07-03 |
| ECLASS 12.0 | 27-40-07-03 |             |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|