

**CD-FLEX 30X30****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

**General ordering data**

Version	Flexible wiring duct, 30 mm x 30 mm, 5.00 mm x 7.50 mm, 500 mm
Order No.	<a href="#">2562790000</a>
Type	CD-FLEX 30X30
GTIN (EAN)	4050118571561
Qty.	50 Stück

## CD-FLEX 30X30

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Height	30 mm	Height (inches)	1.181 inch
Width	30 mm	Width (inches)	1.181 inch
Length	500 mm	Length (inches)	19.685 inch
Net weight	38 g		

### Temperatures

Operating temperature range	-15...80 °C	Operating temperature, min.	-15 °C
Operating temperature, max.	80 °C		

### General information

Colour	grey (similar to RAL 7001)	Flexible wiring duct	Yes
Lid	No	Material	Polypropylene
Non-tracking	Yes	Operating temperature range	-15...80 °C
Slit gap	7.5 mm	Slit width	5 mm
Type of mounting	With adhesive	UL 94 flammability rating	V-2
Version of side panel	slotted		

### Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ECLASS 9.1	27-40-07-03
ECLASS 10.0	27-40-07-03	ECLASS 11.0	27-40-07-03
ECLASS 12.0	27-40-07-03		

### Approvals

ROHS	Conform
------	---------

### Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--