

IE-PI-SCRJ-POF-QA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



FO SC inserts for plug-in connectors ver.1 / 4 / 14

General ordering data

Version	SC insert, Plug SCRJ, POF, reconnectable
Order No.	2564960000
Type	IE-PI-SCRJ-POF-QA
GTIN (EAN)	4050118574647
Qty.	10 Stück

Erstellungs-Datum June 1, 2023 9:34:31 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

IE-PI-SCRJ-POF-QA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	56 mm	Depth (inches)	2.205 inch
Height	10.5 mm	Height (inches)	0.413 inch
Width	13.2 mm	Width (inches)	0.52 inch
Net weight	1.6 g		

Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

General data

Colour	Miscellaneous	Configuration	Connector and flange insert for variant 1, 4 and 14 housings
Connection 1	SCRJ	Connection 2	Screw
Description of article	Plug SCRJ, POF, reconnectable	Dust protection cap material	TPE
Ferrule material	Arcap	Fibre type	POF
Housing main material	PA 66	Insertion loss	≤ 1.0 dB
Plugging cycles	≥ 500	Protection degree	IP67 with housing
Sheath diameter, max.	8 mm	Sheath diameter, min.	5 mm
Single conductor diameter, max	2.3 mm	Single conductor diameter, min	2.1 mm
Type of mounting	Screw mounting		

General standards

Connector standard	IEC 61754-24
--------------------	--------------

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Designation key / Type key
Catalogues	Catalogues in PDF-format