

**HDC MBUS4 F AWG22-20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

Version

Order No. [2565910000](#)

Type HDC MBUS4 F AWG22-20

GTIN (EAN) 4050118575460

Qty. 100 Stück

Erstellungs-Datum June 1, 2023 9:35:05 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## HDC MBUS4 F AWG22-20

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

## Dimensions and weights

Net weight	0.001 g
------------	---------

## Temperatures

Limit temperature	-40 °C ... 90 °C
-------------------	------------------

## General data

Contact surface	Gold-plated	Plugging cycles	≥ 100
Rated current	4 A	Transmission rate	100 MBit/s
Type	Female		

## Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ECLASS 9.0	27-44-02-04
ECLASS 9.1	27-44-02-04	ECLASS 10.0	27-44-02-04
ECLASS 11.0	27-44-02-04	ECLASS 12.0	27-44-02-04

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN</a>
User Documentation	<a href="#">Instructions sheet HDC ModuPlug field attachable</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

HDC MBUS4 F AWG22-20

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Zeichnungen

www.weidmueller.com

