

HDC MBUS4 M AWG18**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Version	
Order No.	2565920000
Type	HDC MBUS4 M AWG18
GTIN (EAN)	4050118575477
Qty.	100 Stück

HDC MBUS4 M AWG18

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 0.001 g

Temperatures

Limit temperature -40 °C ... 90 °C

General data

Contact surface	Gold-plated	Plugging cycles	≥ 100
Rated current	4 A	Transmission rate	100 MBit/s
Type	Pin		

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ECLASS 9.0	27-44-02-04
ECLASS 9.1	27-44-02-04	ECLASS 10.0	27-44-02-04
ECLASS 11.0	27-44-02-04	ECLASS 12.0	27-44-02-04

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

Approvals

ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN
User Documentation	Instructions sheet HDC ModuPlug field attachable
Catalogues	Catalogues in PDF-format

HDC MBUS4 M AWG18

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

