

**ES EPG 60/HPG AEH 25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

**General ordering data**

Version	Crimping tool insert
Order No.	<a href="#">2577810000</a>
Type	ES EPG 60/HPG AEH 25
GTIN (EAN)	4050118590722
Qty.	1 Stück

## ES EPG 60/HPG AEH 25

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	22 mm	Depth (inches)	0.866 inch
Height	42 mm	Height (inches)	1.654 inch
Width	42 mm	Width (inches)	1.654 inch
Net weight	25 g		

### Crimp inserts

Crimp cross-section copper	25	Crimping width	22 mm
Crimping width in mm	22		

### Description of contact

Conductor cross-section, max. AWG	4	Type of contact	Wire-end ferrules with/ without plastic collars
-----------------------------------	---	-----------------	--

### tool data crimping

Cable lug cross section	nominal	25 mm <sup>2</sup>
-------------------------	---------	--------------------

### Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90

### Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--