

**ES EPG 60/HPG AEH 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Crimping tool insert       |
| Order No.  | <a href="#">2577830000</a> |
| Type       | ES EPG 60/HPG AEH 50       |
| GTIN (EAN) | 4050118590708              |
| Qty.       | 1 Stück                    |

## ES EPG 60/HPG AEH 50

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Depth      | 22 mm | Depth (inches)  | 0.866 inch |
| Height     | 42 mm | Height (inches) | 1.654 inch |
| Width      | 42 mm | Width (inches)  | 1.654 inch |
| Net weight | 25 g  |                 |            |

### Crimp inserts

|                            |    |                |       |
|----------------------------|----|----------------|-------|
| Crimp cross-section copper | 50 | Crimping width | 22 mm |
| Crimping width in mm       | 22 |                |       |

### Description of contact

|                                   |   |                 |  |
|-----------------------------------|---|-----------------|--|
| Conductor cross-section, max. AWG | 1 | Type of contact | Wire-end ferrules with/<br>without plastic collars |
|-----------------------------------|---|-----------------|--|

### tool data crimping

|                         |         |                    |
|-------------------------|---------|--------------------|
| Cable lug cross section | nominal | 50 mm <sup>2</sup> |
|-------------------------|---------|--------------------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001282    | ETIM 7.0    | EC001282    |
| ETIM 8.0    | EC001282    | ECLASS 9.0  | 21-04-90-90 |
| ECLASS 9.1  | 21-01-90-90 | ECLASS 10.0 | 21-04-90-90 |
| ECLASS 11.0 | 21-04-90-90 | ECLASS 12.0 | 21-04-90-90 |

### Downloads

Catalogues [Catalogues in PDF-format](#)