

IE-USB-3.0-A-A-3M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

| | |
|------------|---|
| Version | USB cable, USB A 3.0, USB A 3.0, PVC, 3 m |
| Order No. | 2581730030 |
| Type | IE-USB-3.0-A-A-3M |
| GTIN (EAN) | 4050118630534 |
| Qty. | 1 Stück |

Erstellungs-Datum June 2, 2023 11:13:50 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

IE-USB-3.0-A-A-3M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Length | 3 m | Length (inches) | 118.11 inch |
| Net weight | 140 g | | |

Temperatures

| | | | |
|-----------------------------|----------------|-----------------------------|--------|
| Operating temperature | -15 °C...80 °C | Operating temperature, min. | -15 °C |
| Operating temperature, max. | 80 °C | | |

Technical specifications for cable

| | |
|------------------|------|
| Sheathing colour | blue |
|------------------|------|

General technical data

| | |
|-----------------|------------------|
| Contact surface | Gold over nickel |
|-----------------|------------------|

Cable structure

| | | | |
|-----------------------|-------------------------------------|-----------------------|---------|
| Cross-section | 4*AWG30 + 2*AWG30 + 2*AWG20 (Power) | Material sheath | PVC |
| Sheath diameter, max. | 5.65 mm | Sheath diameter, min. | 5.35 mm |
| Sheathing colour | blue | | |

Plug

| | | |
|----------------------------|--|--------------|
| Plug | Cable side | left |
| | Version of contact face | USB A 3.0 |
| | Protection degree (IP) | IP20 |
| | Gender of contact | male contact |
| | Outlet direction | straight |
| | Version of connector | plug |
| | Housing main material | Plastic |
| | Status indicator available | No |
| | Shielding available | Yes |
| | Cable side | right |
| | Version of contact face | USB A 3.0 |
| | Protection degree (IP) | IP20 |
| | Gender of contact | male contact |
| | Outlet direction | straight |
| | Version of connector | plug |
| | Housing main material | Plastic |
| Status indicator available | No | |
| Shielding available | Yes | |
| Plug left | USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded | |
| Plug right | USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded | |

Plug, left

| | | | |
|----------------|--|-----------------------------|------------------|
| Connector left | USB A 3.0 | Contact surface, plug, left | Gold over nickel |
| Plug left | USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded | | |

IE-USB-3.0-A-A-3M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Plug, right

| | | | |
|-----------------|--|-----------------|------------------|
| Connector right | USB A 3.0 | Contact surface | Gold over nickel |
| Plug right | USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001408 | ETIM 7.0 | EC001408 |
| ETIM 8.0 | EC001408 | ECLASS 9.0 | 27-06-20-11 |
| ECLASS 9.1 | 27-06-90-90 | ECLASS 10.0 | 27-06-01-06 |
| ECLASS 11.0 | 27-06-01-06 | ECLASS 12.0 | 27-06-01-06 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|