

## CABTITE CR 24/10 EMV

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Similar to illustration



In combination with a large number of different shield connection clamps (KLBÜ), the shield connection rails enable practical, uncomplicated and fast shielding of cables.

### General ordering data

Version	Shield connection rail, Cabtite (cable entry system), Steel, galvanized, silver, Height: 35.23 mm, Width: 140 mm, Depth: 16 mm
Order No.	<a href="#">2583890000</a>
Type	CABTITE CR 24/10 EMV
GTIN (EAN)	4050118647068
Qty.	10 Stück

Erstellungs-Datum June 2, 2023 11:14:46 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## CABTITE CR 24/10 EMV

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	16 mm	Depth (inches)	0.63 inch
Height	35.23 mm	Height (inches)	1.387 inch
Width	140 mm	Width (inches)	5.512 inch
Diameter	5.3 mm	Mounting dimension - height	5.91 mm
Mounting dimension - width	5.3 mm	Net weight	46.96 g

### General information

Halogen	No	Material	Steel, galvanized
Silicone	No		

### Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ECLASS 9.0	27-18-28-15
ECLASS 9.1	27-18-92-65	ECLASS 10.0	27-18-28-15
ECLASS 11.0	27-18-28-15	ECLASS 12.0	27-18-28-15

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>