

**CBC 15/50 BK****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Similar to illustration**

Spiral and webbing hoses are particularly suitable for the construction of space-saving cable routing systems in switch gears and control cabinets. They are used for guiding, protecting and bundling cables and wires - for example, in the transition between the enclosure interior and the door.

**General ordering data**

Version	Protective cable hose
Order No.	<a href="#">2588480000</a>
Type	CBC 15/50 BK
GTIN (EAN)	4050118602661
Qty.	50 m

## CBC 15/50 BK

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

Length	50,000 mm	Length (inches)	1,968.5 inch
Diameter	15 mm	Net weight	41.86 g

### Temperatures

Operating temperature range	-20...90 °C	Operating temperature, min.	-20 °C
Operating temperature, max.	90 °C		

### General information

Bundle diameter, max.	15 mm	Colour	black, RAL 702 1
Diameter	15 mm	Material	Polypropylene
Nominal diameter	15 mm	Operating temperature range	-20...90 °C
UL 94 flammability rating	HB	Usable cross-section	176 mm <sup>2</sup>

### Classifications

ETIM 6.0	EC002604	ETIM 7.0	EC002604
ETIM 8.0	EC002604	ECLASS 9.1	27-43-03-02
ECLASS 10.0	27-43-03-02	ECLASS 11.0	27-43-03-02
ECLASS 12.0	27-43-03-02		

### Approvals

ROHS	Conform
------	---------

### Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--